

Top Treatment

FLAT VALANCE | DOUBLE FLAT VALANCE



## FLAT VALANCE

Clean and simple, this valance can be used to modernize the setting or to cover a Performance Rollershade.

### INSIDE MOUNT DETAILS

- 6"L. Custom sizes available
- Valance attached to wrapped 1"D x 1"H wood headrail. Other headrail sizes available
- Side returns not available
- 1/8"W deduction
- Unlined; liner not available

### OUTSIDE MOUNT DETAILS

- 4"D x 6"L. Custom sizes available. When placing order, specify the inside box dimensions. Overall width may vary due to wood return and weave thickness (1 1/2"-1 3/4")
- Wrapped wood box frame
- Unlined; liner not available

### DC DESIGN CONSIDERATIONS

- When ordering a valance wider than max seamless width, fabric will be railroaded or seamed vertically



Inside Mount





Outside Mount

## DOUBLE FLAT VALANCE

Fabric falls from both the front and back of the headrail in this valance style. It is an ideal solution for Performance Rollershade concealment, to hide light gaps or conceal component hardware.

### DETAILS

- Inside mount only
- 6"L. Custom sizes available
- Valance attached to a wrapped wood headrail, size must be specified
- Side returns not available
- 1/8"W deduction
- Unlined; liner not available



Inside Mount  
with custom bracket

To finish specifying your Top Treatments, and complete your worksheet, follow this step-by-step process in the [Style Guide](#):

## 1 SELECT TOP TREATMENT STYLE

You're on your way

## 2 SELECT UPGRADES

Liner | Mitered Valance

For assistance with specifying or ordering please contact your local representative showroom or H&F.